

Datasheet**Mobile Industrial Plug**

Stock No:
2144081



Image for reference only


Technical Characteristics

Rated Current:	32
Rated Voltage	200-250
Poles	3P (2P+T)
Clock Position	6h
Rated Frequency	50/60Hz
Insulating Resistance	>10MΩ@500Vdc
Dielectric Stength	2,5kV 60s
IP Protection Degree	IP44 (IEC / EN 60529)
Operating Temperature	-25°C/ 40°C
Glow Wire Test	850°C live parts supports /650°C other parts
Material	Housing: PA6/ABS
Product Standard	IEC/EN 60309-1, IEC/EN 60309-2

Datasheet

Mobile Industrial Plug

Stock No: 2144081



Dimensions in mm

A	B	C	D	E	F	G	ØK
172	73	125	-	-	-	-	11,5-21