

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2144291001](#)
Status: **Active**
Overview: [LTE Cellular Antennas](#)
Description: 5GHz Compatible Hinged External Antenna, with SMA Male Connector, White

Documents:

3D Model	Application Specification 2144290001-000 (PDF)
3D Model (PDF)	Packaging Specification 2135230001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 2144290001-001 (PDF)	



General

Product Family	Antennas
Series	214429
Component Type	External Antenna
Function	Signal
Mates With	SMA Female Receptacle
Overview	LTE Cellular Antennas
Product Name	5G Cellular Antenna
Protocol	Cellular
Type	External Antenna
UPC	193264436095

Physical

Length	171.50mm
Mounting Style	N/A
Net Weight	14.143/g
Packaging Type	PET Bag
Polarization	Linear
Radiation Pattern	Omnidirectional
Width	19.40mm

Electrical

Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	698
Band#2 F_End (MHz)	2690
Band#2 F_Start (MHz)	1710
Band#3 F_End (MHz)	4200
Band#3 F_Start (MHz)	3300
Band#4 F_End (MHz)	5000
Band#4 F_Start (MHz)	4400
Electrical Connectivity	Cable
Peak Gain (dBi)	1.6 @ 698 MHz, 3.5 @ 4400 MHz, 3.6 @ 3300 MHz, 5.5 @ 1710 MHz
Return Loss - S11 (dB)	< -10, < -5
Total Efficiency	>55% @ 4400 MHz, >55% @ 698 MHz, >60% @ 3300 MHz, >70% @ 1710 MHz

Material Info

Reference - Drawing Numbers

Application Specification	2144290001-000
Packaging Specification	2135230001-001
Product Specification	2144290001-001
Sales Drawing	2144290001-000

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
ECHA_01_2020 (16
January 2020)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[214429 Series](#)

This document was generated on 06/09/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION