

#### **FEATURES**

- 2 Part Gland
- High mechanical strength
- -100°C to +300°C

# RS PRO Nickel Plated Brass Male Fixed Flexible Conduit Gland 25mm

RS Stock No.: 2149561



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

**Product Description** 

. \_\_\_\_ .

## Flexible Conduit Gland



## **General Specifications**

Material	Nickel Plated Brass		
Colour	Self Colour		
Conduit Type	Flexible		
Qty per pack	10		
Maximum Operating Temperature	+300°C		
Minimum Operating Temperature	-100°C		
Nominal Size	25mm		
Thread Size	M25		

## **Compatible Conduits**

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
2149592	RS PRO	Flexible Conduit	Galvanised Steel	IP40	-100°C to +300°C
2149583	RS PRO	Flexible Conduit	PVC Coated Galvanised Steel	IP54	-15°C to +70°C