#### Flexible Conduit



### **FEATURES**

- IP40 performance
- Highly Flexible
- High mechanical strength
- -100°C to +300°C
- Manufactured to BS EN 61386

# RS PRO Galvanised Steel Flexible Conduit 20mm – 10 metres

RS Stock No.: 2149587



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

**Product Description** 

.\_\_\_\_.

## Flexible Conduit



## **General Specifications**

Material	Galvanised Steel		
Colour	Self Colour		
Conduit Type	Flexible		
IP Rating	IP40		
Length	10 m		
Maximum Operating Temperature	+300°C		
Minimum Operating Temperature	-100°C		
Nominal Diameter	20mm		
Internal Diameter (ID)	16.8mm		
Outside Diameter (OD)	20.3mm		

## **Compatible Glands**

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
2149559	RS PRO	NPB Fixed Gland	2 part gland	High mechanical strength	-100°C to +300°C
2149560	RS PRO	NPB Swivel Gland	2 part gland	High mechanical strength	-100°C to +300°C