

Datasheet

RS PRO High-Performance HMI. 7 inch, 800x400 TFT LCD. 16k Colours. Ethernet.

Stock No: 215-6605



Technical Specifications:


Hardware:	Cortex A7 528MHz CPU 128M DDRIII RAM + 128M Flash
Resolution:	800x400 TFT LCD 16,000 Colours
Storage:	Support Data Storage U Disk
Interface:	COM 1:RS485/RS422. COM2 RS232, Ethernet USB Host + USB Client. Type A & B
Dimensions:	Bezel; 201.2 x 147.2 x 39.0 Cut-out; 192.0 x 138.0.

Features & Benefits:

- Cortex A7 CPU
- Ethernet
- High Grade picture quality
- Fast screen update & switching
- High Communication stability

Dimensional line drawings

Unit : mm , error range:±0.5mm



Quality Standards

CE
RoHS

General

Model			
General	Screen Size	7 Inch	
	Resolution	800*480	
	Colors	16,000K colors	
	Brightness	250cd/m ²	
	Backlight Type	LED	
	Touch Screen	High precision four-wire resistive	
	Backlight Life Time	50,000 hours	
	CPU	Cortex A7 528MHz	
	Storage	128M FLASH + 128M DDRAM	
	USB Port	USB host + USB Client	
	Ethernet	YES	
	COM	COM1	RS422/RS485
		COM2	RS232
Power	Power	<8w	
	Power Supply	DC 24V (12~28V DC)	
Dimension	Shell	PC+ABS	
	Dimension (mm)	201.2W*147.2H*39.0D	
	Mounting size (mm)	192.0W*138.0H	
	Net/Gross (KG)	0.51/0.74	
Operate Environment	Temperature	Working Temperature : -10~60°C ; Storage Temperature : -20~70°C	
	Humidity	10-85%RH (Non-condensing)	
	Seismic Resistance		IEC61131-2 standard
			Continuous vibration occasion: 10Hz~57Hz 0.075mm, 57Hz~150Hz 9.8m/s ²
	Cooling	Discontinuous vibration: 10Hz~57Hz 0.035mm, 57Hz~150Hz 4.9m/s ² X, Y, Z in 10 directions each (80 minutes)	
Protection		Air cooling	
Protection		IP65 (Front panel)	
CE		CE Marked	
FCC		FCC Class A	