

FEATURES

- High-Temperature strength without sufficient coolant
- 135° non-slip split point for precise centring
- Direct drilling without the need for prior centring or drilling a pilot hole
- Direct drilling without the need for prior centring or drilling a pilot hole
- 5% Cobalt High-Performance HSS-E Drill bits

RS PRO Drill Bit Sets

RS Stock No.: 216-690



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

RS PRO offers this exceptional Drill Bit Set made from HSS-E cobalt alloy for high-performance drill bits. It contains a great selection of the most commonly used diameters. With these High-Speed Steel (HSS) featuring a 5% cobalt content, this allows for increased heat resistance even without insufficient cooling. With the addition of Cobalt in the cutting material, these drill bits can be used on high tensile strength materials of 800N/m². Featuring a 135° non-slip split point is great for precisely centring and manufactured in accordance with DIN 338 for high precision tolerances and geometric accuracies.

General Specifications

Set Type	Jobber Drill Set
Minimum Size	1mm
Maximum Size	13mm
Drilling Application	Metal
Material	HSS-E Cobalt
Number of Pieces	25
Set Contents	HSS Drill Bits
Point Angle	1350 split point
Bit Finish	Amber Finish





Drill Bit Sets





