

FEATURES

- 50 Ω impedance
- Operating frequency is 4GHz
- Insulation: Teflon

RS PRO Straight 50 Coaxial Adapter BNC Socket to BNC Socket 4GHz

RS Stock No.: 218-4244



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

50Ohm BNC radio frequency coaxial baffle jack to jack coupler with bayonet fixing device. The 50Ohm BNC direct-to-socket connector with a nickel-plated body, nut and washer, and a gold-plated central contact.

BNC connector for a variety of applications including video signal transmission and test equipment..

General Specifications

Adapter type	BNC socket to BNC socket
Body Plating	Nickel
The main body position	Straight
Contact Material	Brass
Contact Plating	Gold
Gender	Female
Polarity	Normal

Electrical Specifications

Temperature Range	-65°~+165°
Characteristic Impedance	50Ω
Frequency Range	0~4GHz
Working Voltage	500V
Insulation Resistance	≥1000MΩ
Medium Pressure	1000V(rms)
VSWR	≤1.3
Working Life	500Cycles

Approvals

Declarations	CE
Hazardous Area Certification	
Standards Met	ROHS

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
5464083	RS PRO	Coaxial adapter	50Ω impedance	Operating frequency is 4GHz	

