



Data Sheet
2198133



High CRI Sensor Headtorch

Product Features

Heavy Duty IKo8 High-CRI Sensor Head light
350 lumen 3W COB LED, 96+ CRI
3 x Colour temperatures - 2700k / 4500k / 6500k
Intelligent motion sensor remote activation
Super tough IKo8 shock resistant housing
IP67 dust & water-proof
Easy twist dimmer switch – 10% to 100% brightness
Silicone lined non-slip adjustable headband
60° Rotating angle head
Rechargeable built-in Li-polymer battery
1m Micro-USB charging cable included
3 hour charge time

Battery: 3.7v 1400mAh Li-polymer battery

Product Size: 41 x 86.5 x 48.5 mm

Product Weight: 160 g

Technical Data:

High: 350 lumen / 3.5 hours

Low: 50 lumen / 20 hours

