

Data Sheet 2198138



Hybrid Aluminium Penlight

Product Features

400 Lumen 7500k Aluminium Penlight
Tough aircraft-grade aluminium construction
Easy twist 4 x Flood-to-Spot Twist Zoom
Detachable pocket clip
Rechargeable 750mAh Li-polymer Battery included
USB-type-C charging cable included
2-3 hours charge time
Also works with 2 x AAA Alkaline batteries (not included)
IPX4 water resistant
1m impact resistant

Battery: 3.7v 75omAh Li-polymer (included)

Or 2 x AAA Alkaline batteries (not included)

Product Size: 17.5 x 14.5 x 155mm

Product Weight: 42.3 g

Technical Data: Rechargeable Battery

High Mode 100%: 400 lumen / 75 metres / 1.5 hours Low Mode 10%: 50 lumen / 22 metres / 7 hours

2 x AAA Batteries (not included)

High Mode 100%: 100 lumen / 35 metres / 4 hours Low Mode 10%: 12 lumen / 12 metres / 12 hours



