VALUE UTP Patch Cord, Cat.6 (Class E), yellow, 10 m

Product No. Manufacturer Manufacturer No. EAN (single piece)	21.99.1582 VALUE 21.99.1582 7611990177943	Value
	UTP = UAUTP $UTP = UAUTP$ $FTP = FAUTP$ $UTP = FAUTP$	

aluminium clad fuil / Red: tinned copper braid



Patch cable for networking connections between devices. Prepared unshielded Twisted Pair cable with RJ-45 connectors on both ends. Durable due to moulded kink protection. Flexible cable, suitable for narrow bending. Plugs with gold plated contacts. Contact settings 1:1, in accordance with the EIA/TIA 568 standard. Construction: 4-pair stranded wire.

For a structured cabling system we recommend to use the following components: VALUE Cat.6 UTP Cable, Solid Wire, AWG24, 300 m: 21.99.0995. VALUE Cat.6 Flush/Surface Mount Wall Jack, unshielded, white: 25.99.8494/25.99.8394; VALUE Cat.6 19" Patch Panel, 24 Ports, unshielded: 26.99.0351 (black), 26.99.0352 (grey); VALUE Cat.6 UTP Patch Cord, grey, 5 m: 21.99.0905. Our in-house laboratory has tested this cable-plug combination, in a Channel of 100 meters, in compliance with Class E specifications.

Technical specifications		
Manufacturer	VALUE	
Product group	Twisted Pair Cable	
Product type	UTP Patch Cables	
Colour	yellow	
Length	10 m	
Shield type	UTP	

Transfer quality	Cat6 / Class E
Impedance	100 Ohm
Quantity of wires	8
Conductor type	Wire
Crossed	No
Colour (Spout)	yellow
Cable LSOH	No
Side 1 Connector Type	RJ-45
Side 1 Connector Gender	Male
Side 2 Connector Type	RJ-45
Side 2 Connector Gender	Male
Connector Type RJ45	Standard
Weight	264.6 g
Height of packaging (single piece)	35 mm
Width of packaging (single piece)	145 mm
Depth of packaging (single piece)	145 mm
Package weight (single piece)	0.337 kg