

Components of electronic housing - HC-ALU 6-78 COVER GY - 2200896

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Panel mounting base, length: 15 mm, Side part, color: gray, width: 101.9 mm, height: 36.2 mm

Why buy this product

- ✔ Item is from the HC-ALU product range
- ✔ Aluminum press-drawn section
- ✔ Available in lengths from 100 mm ... 1000 mm, can be individually cut to any length
- ✔ Available in overall widths 53.5 mm ... 161 mm
- ✔ Degree of protection up to IP65
- ✔ Usable as handheld and wall housing
- ✔ Optional EMC seals available



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 716772
GTIN	4046356716772
Weight per Piece (excluding packing)	111.800 g
Custom tariff number	76169910
Country of origin	Hungary

Technical data

General

Housing type	Panel mounting base
Color (RAL)	gray

Dimensions

Length	15 mm
Constructional height	36.2 mm
Width	101.9 mm

Components of electronic housing - HC-ALU 6-78 COVER GY - 2200896

Technical data

Dimensions

Depth	78 mm
-------	-------

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC000721
ETIM 5.0	EC002779
ETIM 6.0	EC002779

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501