

## Components of electronic housing - HC-ALU 6-78 DKL-COVER GY - 2201122

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Panel mounting base, length: 15 mm, Side part, color: gray, width: 101.9 mm, height: 36.2 mm

### Why buy this product

- ✓ Item is from the HC-ALU product range
- ✓ Aluminum press-drawn section
- ✓ Available in lengths from 100 mm ... 1000 mm, can be individually cut to any length
- ✓ Available in overall widths 53.5 mm ... 161 mm
- ✓ Degree of protection up to IP65
- ✓ Usable as handheld and wall housing
- ✓ Optional EMC seals available

RoHS

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 730228
GTIN	4046356730228
Weight per Piece (excluding packing)	96.000 g
Custom tariff number	76169910
Country of origin	Hungary
Note	Made to Order (non-returnable)

### Technical data

#### General

Housing type	Panel mounting base
Color (RAL)	gray

#### Dimensions

Length	15 mm
--------	-------

# Components of electronic housing - HC-ALU 6-78 DKL-COVER GY - 2201122

## Technical data

### Dimensions

Constructional height	36.2 mm
Width	101.9 mm
Depth	78 mm

## Classifications

### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

### ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC000721
ETIM 5.0	EC002779
ETIM 6.0	EC002779

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501