
## Data Sheet | Item Number: 221-423 Splicing connector with levers Green Range; for all conductor types; max. 4 mm<sup>2</sup>; 3conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm<sup>2</sup>; transparent



https://www.wago.com/221-423







### Data Sheet | Item Number: 221-423

https://www.wago.com/221-423



Your Benefits:

- Plastics made partially from post-consumer recycled material (such as recycled PET bottles) and bio-based recyclables from industrial and household use
- Reduced consumption of fossil resources
- Ease of use pull the lever up, insert a conductor and push the lever back down
- Available as 2-, 3- and 5-wire connectors
- Easily terminate conductors from 0.14 to 4 mm<sup>2</sup>
- · Connect solid, stranded and fine-stranded conductors
- Time savings for installers and device manufacturers
- Quickly install devices with higher power consumption
- Safely install long cable runs with larger conductor cross sections
- Mounting carrier for installation conforms to standards
- · Custom carriers are possible

Notes

Safety information

in grounded power lines

# Data Sheet | Item Number: 221-423

https://www.wago.com/221-423



Electrical data			
Ratings per		EN 60664	
Overvoltage category	Ш	III	II
Pollution degree	3	2	2
Nominal voltage	-	-	450 V
Rated surge voltage	-	-	4 kV
Rated current	-	-	32 A

Approvals per		UL 486C	
Use group	В	С	D
Rated voltage	-	600 V	-
Rated current	-	20 A	-

11 mm / 0.43 inches

Side-entry wiring

Connection data				
Connection points	3		Connection 1	
Total number of potentials 1		Connection technology	CAGE CLAMP®	
			Actuation type	Lever
			Connectable conductor materials	Copper
		Nominal cross-section	4 mm² / 12 AWG	
	Solid conductor	0.2 4 mm² / 24 12 AWG		
		Stranded conductor	0.2 4 mm² / 24 12 AWG	
		Fine-stranded conductor	0.14 4 mm² / 24 12 AWG	

Physical data	
Width	18.8 mm / 0.74 inches
Height	8.6 mm / 0.327 inches
Depth	18.8 mm / 0.732 inches

Strip length

Wiring direction

Material data	
Note (material data)	
	Information on material specifications can be found here
Color	transparent
Insulation material	Polycarbonate (PC)
Flammability class per UL94	V2
Fire load	0.075 MJ
Actuator color	green
Weight	2.5 g

Environmental requirements	
Ambient temperature (operation)	+85 °C
Continuous operating temperature	105 °C
Temperature marking per EN 60998	T85

### Data Sheet | Item Number: 221-423

https://www.wago.com/221-423



Commercial data	
PU (SPU)	500 (50) pcs
Country of origin	DE
GTIN	4066966345438
Customs tariff number	85369010000

#### **Environmental Product Compliance**

RoHS Compliance Status

Compliant,No Exemption

Subject to changes. Please also observe the further product documentation!