



Instruction Datasheet

ENGLISH

ANALOGUE TEMPERATURE CONTROLLER

Stock Number:



72 x 72 DIN Size Analogue Set, Analog Temperature Controller

J type Thermocouple Input
ON/OFF Operation
Hysteresis value configurable with Jumper



Specifications

Input

Thermocouple: J type Fe-CuNi, 0...800 °C

Output

Control Output: Relay(5A@250V~ at resistive load)

Environmental Rating and Physical Specification

Storage / Operating Temperature: 0...50°C

Storage / Operating Humidity: 90 % max. (None condensing)

Protection Class : IP65 at front, IP20 at rear.

Supply Voltage

230 V ~ (±%15) 50/60 Hz 4VA

Dimensions

72x72mm

Electrical Wirings

