

FEATURES

- Can be hung on the wall, can be on the ground, to meet the different needs of customers
- The sealing ring is made of German imported polyurethane foam sealing tape
- The door can be installed left and right
- Troughed box edge to prevent water and dust from entering the inside of the box
- IP66 rating

RS PRO Steel Wall Box

RS Stock No.: 222-9359



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS Pro, a range of incredibly useful steel wall mounted enclosures. Enclosures are present in almost every industry and can store all manor of items, such as medical equipment or electronics. These boxes are rated at IP66 and provide an excellent degree of protection, whether it's used within an indoor or outdoor environment. With various sizes available, they are suitable for a wide selection of applications. All models are highly reliable and excellent quality.

General Specifications

Colour	Grey RAL 7032
Door Lock Type	Single Lock System with metal lock LK-5
Thickness	1.2mm for enclosure & door
Chassis Plate	Zinc coated steel 1.5mm
Finish	Paint finish epoxy polyster powder coating textured finish

Mechanical Specifications

Dimensions:	300 H x 200W x 150D mm (ST2 315M)
External Height	300mm
External Width	200mm
External Depth	150mm

Protection Category

IP Rating:	IP66
------------	------

Similar Products

Stock No.	Brand	Product Name	
7755788	RS PRO	Wall Box	K2 plastic lock

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories

