


FEATURES

- UL approved Nylon 66, 94V-2
- Color: Natural, other special colors are available upon request.
- Feature: Low Smoke and Halogen Free cable tie suitable for various industry, also household DIY and gardening.
- Finger catch design to release cable tie locking. Ideal for temporary fastening purpose.
- Easy to thread.

RS PRO Releasable Cable Tie

RS Stock No.: 2243196



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

ATTRIBUTE 1

- Material: UL approved Nylon 66 , 94V-2.
- Color: Natural, other special colors are available upon request.
- Feature: Low Smoke and Halogen Free cable tie suitable for various industry, also household DIY and gardening.
- Finger catch design to release cable tie locking. Ideal for temporary fastening purpose.

General Specifications

Series	Releasable Cable tie
Type	Releasable
Colour	Natural
Material	UL approved Nylon 66
Finish	
Application	
Resistant To	
UV Resistant	No
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	85°C
Fire Behaviour	Self-Extinguishing
Quantity	100

Mechanical Specifications

Length	300mm(11 7/8")
Width	4.8mm
Tensile Strength	50lbs/22kgs
Max. Bundle Dia.	88mm
Thickness	1.6±0.25mm

Protection Category

IP Rating

Classification

eCl@ss (10.0.1)

UNSPSC (6.01)

Approvals

Declarations

Standards Met

RoHS, SVHC, HF, ABS

Similar Products

Stock No.	Brand	Product Name	Colour	Material	Tensile strength

