

## FEATURES

- A2 stainless steel
- Hex socket cap socket screws
- Supplied in a polypropylene case with a hinged lid

# 431 piece Stainless Steel Screw/Bolt Kit, M10, M12, M6, M8

RS Stock No.: 225-3341



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

From the trusted RS PRO brand, this set of high-quality slotted pan and flat machine screws are ideal for many applications. This set also includes washers and nuts in corresponding sizes for the pan head screws.

### General Specifications

<b>Number Of Pieces</b>	431
<b>Screw/Bolt Type</b>	Socket Screw
<b>Head Shape</b>	Hex Socket cap
<b>Drive Type</b>	Slot
<b>Kit Contents</b>	M10, M12, M6, M8 Screws
<b>Applications</b>	Carpentry, Construction and roofing, DIY applications, Machinery applications

### Mechanical Specifications

<b>Screw/Bolts Lengths</b>	12mm to 60mm
<b>Thread Size</b>	M10, M12, M6, M8
<b>Material</b>	Stainless Steel
<b>Stainless Steel Type</b>	A2 304
<b>Finish</b>	Plain
<b>Screw/Bolt Length Longest</b>	60mm
<b>Screw/Bolt Length Shortest</b>	12mm

Kit Contents										
Thread Size	L (mm)	Qty	L (mm)	Qty	L (mm)	Qty	L (mm)	Qty	L (mm)	Qty
M6	12	40	16	30	20	65	25	55	40	50
M8	16	20	20	20	25	25	30	25	-	-
M10	20	20	30	20	40	20	60	15	-	-
M12	20	10	40	10	60	6	-	-	-	-