

FEATURES

- Designed using strong polyethylene (PE)
- Easy to assemble – no tools are required
- Moisture resistant and impact proof - will not rust
- Easy to Clean
- Four non-marking wheels

RS PRO 2 Shelf PE Trolley Trolley, 810 x 610mm, 180kg Load

RS Stock No.: 225-6003



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS Pro Plastic shelf trolleys (or carts) are great for transporting goods and create greater mobility throughout the workplace. The trolley is easy to move around with the four swivel castor wheels of which two have brakes, to ensure you can lock it securely in place. The top shelf of the trolley is fitted with two hand grips. This trolley is made up of three anti-slip shelves with lipped edges in polypropylene (PE) making it suitable for harsh environments.

General Specifications

Type	Shelf
Number of Levels	2
Wheel Type	Rubber
Wheel Features	Braked, Non-Marking, Swivel
Frame Material	PE
Wheel Material	Rubber
Brakes	Yes
Applications	Canteens, Offices, Workshops, Warehouses, Garages

Mechanical Specifications

Lipped Edge Height on Shelf	12mm
Load Capacity	180kg
Wheel Diameter	100mm
Shelf Clearance Between Each Shelf	630mm

Trolley Size	
Dimension	860mm x 885mm x 610mm
Depth	610mm
Width	885mm
Height	860mm

External Shelf Size	
Platform Dimension	810mm x 610mm
Platform Length	810mm
Platform Width	610mm

Internal Shelf Size	
Dimension	812mm x 595mm
Length	812mm
Width	595mm



UTILITY TRAY TROLLEY RANGE								
Trolley Size HxWxD (mm)	No. of Shelves	External Shelf Size LxW (mm)	Internal Shelf Size LxW (mm)	Lipped Edge Height on Shelf (mm)	Shelf Clearance Between Each Shelf (mm)	Wheel Dia (mm)	Capacity (Kgs)	RS Stock No.
860 x 670 x 460	3	610 x 460	595 x 444	6	315	100	150	2255971
860 x 670 x 460	3	610 x 460	595 x 444	6	315	100	150	4442391
860 x 885 x 610	2	810 x 610	812 x 595	12	630	100	180	2256003
835 x 885 x 610	3	810 x 610	812 x 595	12	275	100	180	2256019
975 x 885 x 610	3	810 x 610	812 x 595	12	275	200	350	7898548