

## **FEATURES**

- Grease-free surface
- Smooth
- Light weight
- Self-adhesive cable tie mount

# RS PRO Self Adhesive Natural Cable Tie Mount 29 mm x 29mm, 5mm Max. Cable Tie Width

RS Stock No.: 229-560



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



# **Product Description**

This adhesive cable tie base is designed as an anchor point to attach cables to another surface using a cable tie. For increased support, mounting holes are provided for screws. Its 4-way design enables you to thread cable ties either vertically or horizontally once mounted.

The mounts are manufactured from nylon 6.6 (also known as Nylon 66) that is classified to UL 94V-2, making them ideal for use where fire resistance is critical. Cable tie mounts have been designed specifically to be used with cables and wires to secure, identify and tidy cables.

### **General Specifications**

Series	HC			
Colour	Natural			
Material	Nylon 66			
Minimum Operating Temperature	-28°C			
Maximum Operating Temperature	+48°C			
Quantity	50			
Fire Behaviour	Self-Extinguishing			
Self Adhesive	Yes			
Fixation Method	Screw Mounting			
Application	Cable management and organisation			

### **Mechanical Specifications**

Length	29mm	
Width	29mm	
Fixing Hole Diameter	5mm	
Cable Tie Width Acceptance	5mm	

### **Approvals**

Standards Met	UL 94V-2
---------------	----------





### **Dimensions**



RS Article	Colour	Length (mm)	Width (mm)	Height (mm)		Cable Tie Capacity (mm)
229-560	Natural	29.2	29.2	5.4	5.0	5.5