

Coaxial Panel Connector 22_BNC-50-0-3/133_N

Description

Straight bulkhead receptacle jack

Interface standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Number of matings	500
Weight	0.0111 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00010695
Catalogue drawing	DCA-00010697
Mounting hole	DOU-00010411

Ordering Information

Single package	22_BNC-50-0-3/133_NE
Bulk 100 pcs package	22_BNC-50-0-3/133_NH

Remarks

Front mount chassis connector With panel seal