

FEATURES

- Saddle design offers excellent stability
- Available in black and white colours in a range of sizes
- Simple cable mounting
- Self-extinguishing UL 94 V-2

RS PRO Black Cable Tie Mount 10 mm x 15mm, 4.8mm Max. Cable Tie Width

RS Stock No.: 233-663



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Saddle style screw-mounted cable tie bases, available in black and white for outdoor and indoor use respectively. The clamps are manufactured from nylon 6.6 (also known as Nylon 66) that is classified to UL 94V-2, making them ideal for use where fire resistance is critical. Cable tie mounts have been designed specifically to be used with cables and wires to secure, identify and tidy cables.

General Specifications

Series	HC		
Colour	Black		
Material	Nylon 66		
Minimum Operating Temperature	-45°C		
Maximum Operating Temperature	85°C		
Quantity	250		
Fire Behaviour	Self-Extinguishing		
Self-Adhesive	No		
Fixation Method	Screw Mounting		
Mounting Screw Type	Saddle		
Application	Cable management and organisation		

Mechanical Specifications

Length	15mm
Width	10mm
Fixing Hole Diameter	3.5mm
Cable Tie Width Acceptance	4.8mm
Height	7mm


Approvals

Standards Met UL 94 V-2









RS Stock					
No	H	L	W	T	В
666-717	7	15	10	5.1	3
666-739	9.8	23	16	9	6.3
233-663	7	15	10	5.1	3
233-685	9.8	23	16	9	6.3