

Datasheet

Stock No: 2346922

RS PRO Radial Deep Groove Ball Bearing With Double Shields Stainless Steel



Radial Deep Groove Ball Bearing With Double Shields Stainless Steel

Specifications:

Basic dimensions

Inner diameter [d]	8 mm
Outer diameter [D]	16 mm
Width [B]	5 mm

Physical properties

Load rating dynamic [Cr]	1260 n
Load rating static [C0r]	590 n
Limiting speed grease	40000 rpm
Limiting speed oil [rpm]	47000 rpm

Other data

Radius min [r]	0.2 mm
Seal type	Two metal shields ZZ
Weight	0.0030 kg