

## FEATURES

- Filter / regulator / lubricator
- Manual drain

# RS PRO

## Filter / regulator / lubricator

RS Stock No.: 2351106



Manual Drain

### Product Description

Part No.	Body Size	Port Size	Flow Rate (l/min)
2351106	2000	1/4"	960

## Features

- Filter / regulator / lubricator
- Manual drain

## General Specifications

<b>Max. working pressure</b>	10 bar
<b>Temperature range</b>	+5°C to +60°C
<b>Filter precision</b>	5 micron
<b>Max. inlet pressure</b>	15 bar
<b>Adjustable pressure range</b>	0.5 to 8.5 bar

## Materials

<b>Bowl</b>	Polycarbonate
-------------	---------------