

LED Perm./Blinking Beacon RGB EMDC MC



Part No.:	240.110.50
Series:	240



MECHANICAL DATA		
Height	71mm	
Diameter	55mm	
Materials	PC PC/ABS	
Cap colour	Clear	
Housing colour	Black	
Protection category	IP65	
Connection	Cable	
Tension relief	Pull-out protection	
Type of fixing	Built-in mounting	
Service life optical	50,000 h maximum	
Working temperature minimum	-20℃	
Working temperature maximum	+50℃	

ELECTRICAL DATA		
Operating Voltage	10-30V	
Operating Voltage type	DC	
Rated operating current	60mA	
Rated incrush current	<700mA	
Operating voltage tolerance	+/-0%	


OPTICAL DATA		
Light source	LED	
Light colour	Multicolour	
Optical signal image	Blink Permanent	
Blink frequency	1,00Hz	

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.



LED Perm./Blinking Beacon RGB EMDC MC

OTHER SPECIFICATIONS	
Note	All specifications refer to Unom and room temperature. The advice contained in the installation instruction is to be observed.
Regulations	Conforms to current EU Directives.



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.