

Lexmark Supplies

Your Printer's Best Friend



Compatibility Table

May 2010

LEXMARK MONOCHROME LASER SUPPLIES



Printers Models	Return Programme Cartridges				Regular Cartridges			Other Supplies	
	Extra High Yield Print / Toner Cartridge	High Yield Print/ Toner Cartridge	Print/ Toner Cartridge	Label Print Cartridge	Extra High Yield Print / Toner Cartridge	High Yield Print/ Toner Cartridge	Print/ Toner Cartridge	Staples	Photoconductor Unit
Lexmark 4019, 4028, 4029						1380520 9,500 Pages ⁽¹⁾			
Lexmark 4039						1380950 12,800 Pages ⁽¹⁾	1380850 7,000 Pages ⁽¹⁾		
Lexmark 4039 10plus, Opra/plus						1382150 14,000 Pages ⁽¹⁾	1382100 7,000 Pages ⁽¹⁾		
Lexmark E120/n			12016SE 2,000 Pages ⁽²⁾				12036SE 2,000 Pages ⁽⁴⁾		12026XW 25,000 Pages ⁽²⁾
Lexmark E210							10S0150 2,000 Pages ⁽⁴⁾		
Lexmark E220			12S0400 2,500 Pages ⁽²⁾				12S0300 2,500 Pages ⁽⁴⁾		
Lexmark E232/t, E240/n			24016SE 2,500 Pages ⁽²⁾				24036SE 2,500 Pages ⁽⁴⁾		12A8302 30,000 Pages ⁽²⁾
Lexmark E250d/dn			E250A11E 3,500 Pages ⁽²⁾				E250A21E 3,500 Pages ⁽⁴⁾		E250X22G 30,000 Pages ⁽²⁾
Lexmark E260d/dn			E260A11E 3,500 Pages ⁽²⁾				E260A21E 3,500 Pages ⁽⁴⁾		E260X22G 30,000 Pages ⁽²⁾
Lexmark E320, E322/n		08A0478 6,000 Pages ⁽²⁾	08A0476 3,000 Pages ⁽²⁾			08A0477 6,000 Pages ⁽⁴⁾	08A0475 3,000 Pages ⁽⁴⁾		
Lexmark E321, E323/n		12A7405 6,000 Pages ⁽²⁾	12A7400 3,000 Pages ⁽²⁾			12A7305 6,000 Pages ⁽⁴⁾	12A7300 3,000 Pages ⁽⁴⁾		
Lexmark E330, E332n/tn, E340, E342n/tn		34016HE 6,000 Pages ⁽²⁾	24016SE 2,500 Pages ⁽²⁾			34036HE 6,000 Pages ⁽⁴⁾	24036SE 2,500 Pages ⁽⁴⁾		12A8302 30,000 Pages ⁽²⁾
Lexmark E350d, E352dn		E352H11E 9,000 Pages ⁽²⁾	E250A11E 3,500 Pages ⁽²⁾			E352H21E 9,000 Pages ⁽⁴⁾	E250A21E 3,500 Pages ⁽⁴⁾		E250X22G 30,000 Pages ⁽²⁾
Lexmark E360d/dn		E360H11E 9,000 Pages ⁽²⁾	E260A11E 3,500 Pages ⁽²⁾			E360H21E 9,000 Pages ⁽⁴⁾	E260A21E 3,500 Pages ⁽⁴⁾		E260X22G 30,000 Pages ⁽²⁾
Lexmark E450dn		E450H11E 11,000 Pages ⁽²⁾	E450A11E 6,000 Pages ⁽²⁾			E450H21E 11,000 Pages ⁽⁴⁾	E450A21E 6,000 Pages ⁽⁴⁾		E250X22G 30,000 Pages ⁽²⁾
Lexmark E460dn/dw	E460X11E 15,000 Pages ⁽²⁾	E360H11E 9,000 Pages ⁽²⁾	E260A11E 3,500 Pages ⁽²⁾		E460X21E 15,000 Pages ⁽⁴⁾	E360H21E 9,000 Pages ⁽⁴⁾	E260A21E 3,500 Pages ⁽⁴⁾		E260X22G 30,000 Pages ⁽²⁾
Lexmark E462dtn	E462U11E 18,000 Pages ⁽²⁾	E360H11E 9,000 Pages ⁽²⁾	E260A11E 3,500 Pages ⁽²⁾		E462U21G 18,000 Pages ⁽⁴⁾	E360H21E 9,000 Pages ⁽⁴⁾	E260A21E 3,500 Pages ⁽⁴⁾		E260X22G 30,000 Pages ⁽²⁾
Lexmark Opra E/Ep/Es/E+							69G8256 3,000 Pages ⁽¹⁾		69G8257 20,000 Pages ⁽²⁾
Lexmark Opra E310/E312/E312L						13T0101 6,000 Pages ⁽¹⁾	13T0301 3,000 Pages ⁽¹⁾		
Lexmark Opra K 1220							11A4097 10,000 Pages ⁽²⁾ 12A4605 5,000 Pages ⁽¹⁾		11A4096 32,500 Pages ⁽²⁾
Lexmark Opra M410/M410n						17G0154 15,000 Pages ⁽⁴⁾ 4K00199 10,000 Pages ⁽⁴⁾	17G0152 5,000 Pages ⁽⁴⁾		
Lexmark Opra M412/M412n						17G0154 15,000 Pages ⁽⁴⁾	17G0152 5,000 Pages ⁽⁴⁾		
Lexmark Opra S 1250/S 1255/S 1620/S 1625/S 1650/S 1855/S 2420/S 2450/S 2455		1382925 17,600 Pages ⁽⁷⁾	1382920 7,500 Pages ⁽⁷⁾	1382929 17,600 Pages ⁽⁷⁾		1382625 17,600 Pages ⁽¹⁾			
Lexmark Opra Se 3455			12A0825 23,000 Pages ⁽⁷⁾	12A0829 23,000 Pages ⁽⁷⁾			12A0725 23,000 Pages ⁽⁷⁾		

LEXMARK MONOCHROME LASER SUPPLIES



Printers Models	Return Programme Cartridges				Regular Cartridges			Other Supplies	
	Extra High Yield Print / Toner Cartridge	High Yield Print/ Toner Cartridge	Print/ Toner Cartridge	Label Print Cartridge	Extra High Yield Print / Toner Cartridge	High Yield Print/ Toner Cartridge	Print/ Toner Cartridge	Staples	Photoconductor Unit
Lexmark Optra T610/T610n/T612/T614/T614n/ T614ni/T616/T616n		12A5845 25,000 Pages ⁽²⁾	12A5840 10,000 Pages ⁽²⁾	12A5849 25,000 Pages ⁽²⁾		12A5745 25,000 Pages ⁽²⁾	12A5740 10,000 Pages ⁽²⁾		
Lexmark Optra W810/W810dn/W810n							12L0250 20,000 Pages ⁽²⁾		12L0251 90,000 Pages ⁽²⁾
Lexmark T420d/dn		12A7415 10,000 Pages ⁽²⁾	12A7410 5,000 Pages ⁽²⁾			12A7315 10,000 Pages ⁽²⁾	12A7310 5,000 Pages ⁽²⁾		
Lexmark T430d/dn		12A8425 12,000 Pages ⁽²⁾	12A8420 6,000 Pages ⁽²⁾			12A8325 12,000 Pages ⁽²⁾	12A8320 6,000 Pages ⁽²⁾		
Lexmark T520d/dn/n, T522/dn/n, X520, X522/s		12A6835 20,000 Pages ⁽²⁾	12A6830 7,500 Pages ⁽²⁾	12A6839 20,000 Pages ⁽²⁾		12A6735 20,000 Pages ⁽²⁾	12A6730 7,500 Pages ⁽²⁾		
Lexmark T620/dn/in/n, T622/dn/in/n, X620e		12A6865 30,000 Pages ⁽²⁾	12A6860 10,000 Pages ⁽²⁾	12A6869 30,000 Pages ⁽²⁾		12A6765 30,000 Pages ⁽²⁾	12A6760 10,000 Pages ⁽²⁾		
Lexmark T630/VE/dn/n/n VE, X630		12A7462 21,000 Pages ⁽²⁾	12A7460 5,000 Pages ⁽²⁾	12A7468 21,000 Pages ⁽²⁾		12A7362 21,000 Pages ⁽²⁾	12A7360 5,000 Pages ⁽²⁾		
Lexmark T632/dtn/n/tn, T634/dn/dtn/dtnf/n/tn, X632/e/s, X634dte/e	12A7465 32,000 Pages ⁽²⁾	12A7462 21,000 Pages ⁽²⁾	12A7460 5,000 Pages ⁽²⁾	12A7468 21,000 Pages ⁽²⁾	12A7365 32,000 Pages ⁽²⁾	12A7362 21,000 Pages ⁽²⁾	12A7360 5,000 Pages ⁽²⁾	11K3188 9,000 Per Box	
Lexmark T640/dn/dtn/n, T642/dtn/n/tn		64016HE 21,000 Pages ⁽²⁾	64016SE 6,000 Pages ⁽²⁾	64004HE 21,000 Pages ⁽²⁾		64036HE 21,000 Pages ⁽²⁾	64036SE 6,000 Pages ⁽²⁾	11K3188 9,000 Per Box	
Lexmark T644/dtn/n/tn	64416XE 32,000 Pages ⁽²⁾	64016HE 21,000 Pages ⁽²⁾	64016SE 6,000 Pages ⁽²⁾	64004HE 21,000 Pages ⁽²⁾	64436XE 32,000 Pages ⁽²⁾	64036HE 21,000 Pages ⁽²⁾	64036SE 6,000 Pages ⁽²⁾	11K3188 9,000 Per Box	
Lexmark T650dn/dtn/n, T652dn/dtn/n		T650H11E 25,000 Pages ⁽²⁾	T650A11E 7,000 Pages ⁽²⁾	T650H04E 25,000 Pages ⁽²⁾		T650H21E 25,000 Pages ⁽²⁾	T650A21E 7,000 Pages ⁽²⁾	25A0013 15,000 Per Box	
Lexmark T654dn/dtn/n, T656dne, T656dne	T654X11E 36,000 Pages ⁽²⁾	T650H11E 25,000 Pages ⁽²⁾	T650A11E 7,000 Pages ⁽²⁾	T650H04E 25,000 Pages ⁽²⁾ T654X04E 36,000 Pages ⁽²⁾	T654X21E 36,000 Pages ⁽²⁾	T650H21E 25,000 Pages ⁽²⁾	T650A21E 7,000 Pages ⁽²⁾	25A0013 15,000 Per Box	
Lexmark W812/dtn/tn							14K0050 12,000 Pages ⁽²⁾		
Lexmark W820/dn/n, X820e							12B0090 30,000 Pages ⁽²⁾		
Lexmark W840/dn/n							W84020H 30,000 Pages ⁽²⁾	25A0013 15,000 Per Box	W84030H 60,000 Pages ⁽¹⁰⁾
Lexmark W850dn/n						W850H21G 35,000 Pages ⁽²⁾		25A0013 15,000 Per Box	W850H22G 60,000 Pages ⁽¹⁰⁾
Lexmark X203n, X204n			X203A11G 2,500 Pages ⁽²⁾				X203A21G 2,500 Pages ⁽²⁾		X203H22G 25,000 Pages ⁽²⁾
Lexmark X215							18S0090 3,200 Pages ⁽²⁾		
Lexmark X264dn, X363dn, X364dn/dw		X264H11G 9,000 Pages ⁽²⁾	X264A11G 3,500 Pages ⁽²⁾			X264H21G 9,000 Pages ⁽²⁾	X264A21G 3,500 Pages ⁽²⁾		E260X22G 30,000 Pages ⁽²⁾
Lexmark X340			X340A11G 2,500 Pages ⁽²⁾				X340A21G 2,500 Pages ⁽²⁾		X340H22G 30,000 Pages ⁽²⁾
Lexmark X342n		X340H11G 6,000 Pages ⁽²⁾	X340A11G 2,500 Pages ⁽²⁾			X340H21G 6,000 Pages ⁽²⁾	X340A21G 2,500 Pages ⁽²⁾		X340H22G 30,000 Pages ⁽²⁾
Lexmark X422		12A4715 12,000 Pages ⁽²⁾	12A4710 6,000 Pages ⁽²⁾			12A3715 12,000 Pages ⁽²⁾	12A3710 6,000 Pages ⁽²⁾		
Lexmark X463de, X464de, X466de/dte/dwe	X463X11G 15,000 Pages ⁽²⁾	X463H11G 9,000 Pages ⁽²⁾	X463A11G 3,500 Pages ⁽²⁾		X463X21G 15,000 Pages ⁽²⁾	X463H21G 9,000 Pages ⁽²⁾	X463A21G 3,500 Pages ⁽²⁾		E260X22G 30,000 Pages ⁽²⁾
Lexmark X642e		X644H11E 21,000 Pages ⁽²⁾	X644A11E 10,000 Pages ⁽²⁾			X644H21E 21,000 Pages ⁽²⁾	X644A21E 10,000 Pages ⁽²⁾		
Lexmark X644e, X646dte/e/ef	X644X11E 32,000 Pages ⁽²⁾	X644H11E 21,000 Pages ⁽²⁾	X644A11E 10,000 Pages ⁽²⁾		X644X21E 32,000 Pages ⁽²⁾	X644H21E 21,000 Pages ⁽²⁾	X644A21E 10,000 Pages ⁽²⁾	11K3188 9,000 Per Box	
Lexmark X651de, X652de		X651H11E 25,000 Pages ⁽²⁾	X651A11E 7,000 Pages ⁽²⁾	X651H04E 25,000 Pages ⁽²⁾		X651H21E 25,000 Pages ⁽²⁾	X651A21E 7,000 Pages ⁽²⁾		
Lexmark X654de, X656de/dte, X658dfe/dme/ dtfe/dtme	X654X11E 36,000 Pages ⁽²⁾	X651H11E 25,000 Pages ⁽²⁾	X651A11E 7,000 Pages ⁽²⁾	X651H04E 25,000 Pages ⁽²⁾ X654X04E 36,000 Pages ⁽²⁾	X654X21E 36,000 Pages ⁽²⁾	X651H21E 25,000 Pages ⁽²⁾	X651A21E 7,000 Pages ⁽²⁾	25A0013 15,000 Per Box	
Lexmark X850e/e VE3/e VE4, X852e, X854e							X850H21G 30,000 Pages ⁽²⁾	21Z0357 20,000 Per Box 25A0013 15,000 Per Box	X850H22G ⁽¹⁰⁾
Lexmark X860de, X862de, X864de						X860H21G 35,000 Pages ⁽²⁾		21Z0357 20,000 Per Box 25A0013 15,000 Per Box	X860H22G ⁽¹⁰⁾

The following supplies are designed for use only in Europe, Middle East and Africa: E120, E232, E330, E332, E240, E340, E250, E350, E352, E450, E260, E360, E460, T640, T642, T644, T650, T652, T654, X642, X644, X646, X651, X652, X654, X656, X658.

(1) Based on approximately 5% print coverage. (2) Average standard page yield value declared in accordance with ISO/IEC 19752. Use and return empty only to Lexmark. (3) Actual Yield may vary based on factors such as number of pages per print job, device speed, paper size and feed orientation, toner coverage, tray source, percentage of black-only printing and average print job complexity. (4) Average standard page yield value declared in accordance with ISO/IEC 19752. (5) Photoconductor maximum yield estimate based on 3 average letter/A4-size pages per print job. Actual Yield may vary based on other factors such as device speed, paper size and feed orientation, toner coverage, tray source, percentage of black-only printing and average print job complexity. (6) 2 x 5,000 pages based on approximately 5% print coverage. (7) Use and return empty only to Lexmark. Based on approximately 5% print coverage. (8) Based on approximately 5% print coverage at comparable industry setting (toner darkness setting 5). (9) Use and return empty only to Lexmark. Based on approximately 5% print coverage at comparable industry setting (toner darkness setting 5). (10) Photoconductor maximum yield estimate based on 6 average letter/A4-size pages per print job. Actual Yield may vary based on other factors such as device speed, paper size and feed orientation, toner coverage, tray source, percentage of black-only printing and average print job complexity.