



Every part matters

RS PRO Wall Mount Enclosures Stainless Steel

RS Stock No: see below



TECHNICAL SPECIFICATIONS

Material	Stainless Steel EN 1.4301 / AISI 304
Surface Finish	Grinded (Grain 240)
Thickness	1.2 mm
IP Rating	IP66, EN60529
Impact Rating	IK 10 (20 Joules)
Gasket	VMQ (Silicon)
Service Temperature	-40°C to +80°C
Lid Screw	Stainless Steel 1.4301 (A2), Captive
Tightening Torque	2 to 4 Nm

ENCLOSURE SIZES

	Length (mm)	Width (mm)	Height (mm)
2410776	100	100	61
2410786	150	100	61
2410787	150	150	81
2410788	200	100	61
2410789	200	200	81
2410790	200	200	121
2410791	300	150	81
2410792	300	200	81
2410793	300	200	121
2410777	300	300	121
2410778	300	300	161
2410779	380	380	161
2410780	400	150	81
2410781	400	200	121
2410782	400	300	161
2410783	500	300	161
2410784	500	400	161
2410785	600	200	121