

Features

- Ratchet crimping tool
- Ring Terminals
6mm to 150mm
- Splice Connectors
6mm to 70mm

RS PRO Ratchet Crimper

RS Stock No.: 241-4710



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Heavy duty ratchet crimping tool for RS PRO terminals. The product is designed for RS PRO Uninsulated Tubular Ring Terminals 6mm to 150mm & RS PRO butt wire splice connectors 6mm to 70mm.

- Copper tube terminal
- Hexagonal crimp
- Simple crimping and release mechanism

General Specifications

Crimp Tool Type	Crimp Tool Frame
For Use With	RS PRO Terminals
Ratcheting	Yes

Mechanical Specifications

Overall Length	440 mm
Wire Size (mm ²)	6 to 150 mm ²
Wire Size (AWG)	10/11, 7, 5, 3, 2, 1/0, 2/0, 3/0, 4/0, 300
Crimping Force	55KN
Rated Operating Pressure	Approx 60 KN
Life span, cycles	10,000 +
Weight	2.45kg
Crimp nest	Max 120 mm ²
Handle spread (closed)	130 mm/5.12 inch
Handle spread (open)	458 mm/18.03 inch
Handle opening angle	125°
Maximum handle force	Approx 25kg
Standard Die Length	30mm
Standard Die width	30mm
Standard Die Height	12mm
Maximum contact diameter	4mm

