

FEATURES

- Backing adhesive from Nitto, no loss in performance
- Flexible silicone with etched foil heating elements
- Fits to irregularly shaped objects
- Operating temperature +200°C (maximum)
- All units supplied with instruction leaflet

RS PRO Silicone Heater Mat, 400 W, 200 x 300mm, 240 V ac

RS Stock No.: 245-663



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Heater mats designed for areas where standard heating methods are difficult to apply. All mats are self-adhesive and have etched foil elements embedded into a glass cloth supported rubber compound. These features provided you with a highly robust but flexible product. The range includes standard rectangular or circular mats powered at a range of voltages at various power ratings.

240 V ac type mats have a circular hole in the centre which can accept a bimetallic thermostat such as stock no. 339 -291

General Specifications

Mat Shape	Rectangle
Applications	Production of heaters; Automotive Industries; GRP (Glass Reinforced Plastic) repairs; Heating lower / medium temperature drums, cylinders, flat plates, water basins or food process machinery

Electrical Specifications

Power Rating	400W
Supply Voltage	240V ac

Mechanical Specifications

Rectangular Mat Size	200mm x 300mm
-----------------------------	---------------

Operation Environment Specifications

Peak Temperature	+300°C
-------------------------	--------

Approvals

Compliance/Certifications

CE / 2011/65/EU and 2015/863

