

FEATURES

- 75 Ω impedance
- Operating frequency is 250Hz
- Nickel plated body provides high load structure quality
- Gold-plated contacts ensure maximum efficiency

RS PRO Family Name

RS Stock No.: 2469516



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These coaxial adapters are designed to provide an efficient means of connecting coaxial cable assemblies through panel mounting connections.

These connectors are made from industry-standard components and are most commonly used to connect radio and television broadcasting equipment.

Coaxial adapters are available for a variety of radio frequency (RF) signal applications as well as medical and test equipment.

General Specifications

Adapter Type	RCA Plug to BNC Socket
Adapter Type A	RCA
Adapter Type B	BNC
Gender A	Male
Gender B	Female
Body Orientation	Straight
Body Plating	Nickel 100u''
Body Material	Brass
Contact Material	Brass
Contact Plating	Gold
Insulation Material	PTFE

Electrical Specifications

Temperature Range	-40°~+85°
Characteristic Impedance	75Ω
Frequency Range	0~250Hz
Working Life	500Cycles

Protection Category

--	--

Additional Information

EAN	
Custom Tariff Number	

Classification

eCl@ss (Version)	
UNSPSC (Version)	

Approvals

Declarations	CE
Hazardous Area Certification	
Standards Met	ROHS

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
7902809	RS PRO	RF Adapter	75Ω impedance	Operating frequency is 250Hz	

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories

