

Pliers with tether attachment point

Complete range



	Article No.	Description
Pliers range with tether attachment point for a tool tether		
	02 02 225 T black atramentized; head polished	High Leverage Combination Pliers, 35 % energy saved compared to conventional combination pliers due to optimised transmission
	08 22 145 T black atramentized; head polished	Needle-Nose Combination Pliers, Slim head for use in inaccessible work areas
	09 02 240 T black atramentized; head polished	Lineman's Pliers, american style, requires 50% less effort compared with conventional combination pliers
	09 12 240 T black atramentized; head polished	09 12 240 T: with cable pulling device and universal mandrel crimp
	13 05 160 T chrome plated	Electricians' Pliers, For gripping, bending, cutting wire and crimping end sleeves (ferrules)
	13 82 200 T black atramentized; head polished	Pliers for Electrical Installation, multifunctional pliers for the electrical installation
	26 12 200 T black atramentized; head polished	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers), Extremely durable, elastic precision tips; half-round, long, pointed jaws; straight
	26 15 200 T chrome plated	
	26 22 200 T black atramentized; head polished	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers), Extremely durable, elastic precision tips; half-round, long, pointed jaws; bent
	26 25 200 T chrome plated	
	70 05 160 T chrome plated	Diagonal Cutter, Slim head for use in inaccessible work areas; with fall protection mechanism, available in compact 160 mm length and robust 180 mm length
	70 05 180 T chrome plated	
	71 02 200 T black atramentized	KNIPEX CoBolt®, Compact Bolt Cutters, Particularly high cutting performance with little physical effort
	71 22 200 T black atramentized	71 22 200 T: 20° angled head with single-sided joint bar and diagonal cutting edge for flush cutting
	71 32 200 T black atramentized	71 32 200 T: Recess in the blade for cutting thicker wire
	73 05 160 T chrome plated	KNIPEX X-Cut®, Compact Diagonal Cutter, For the toughest, sustained use

	Article No.	Description
Pliers range with tether attachment point for a tool tether		
	74 02 200 T black atramentized; head polished	High Leverage Diagonal Cutters, high cutting performance with minimum effort; Available with fall protection in 200 mm and 250 mm lengths
	74 02 250 T black atramentized; head polished	
	74 22 200 T black atramentized; head polished	74 22 200 T: 12° angled head in a 200 mm length
	74 22 250 T black atramentized; head polished	74 22 250 T: 12° angled head in a 250 mm length
	86 05 180 T chrome plated	Pliers Wrenches, pliers and a wrench in a single tool, for damage free installation of plated fittings; Available with fall protection in a compact 180 mm a classic 250 mm length
	86 05 250 T chrome plated	
	87 02 180 T grey atramentized; head polished	KNIPEX Cobra®, Hightech Water Pump Pliers, push the button for adjustment on the workpiece; self-locking on pipes and nuts; Available with fall protection in a compact 180 mm length, a classic 250 mm length and in a 300 mm length for greater leverage
	87 02 250 T grey atramentized; head polished	
	87 02 300 T grey atramentized; head polished	
	88 02 250 T black atramentized; head polished	KNIPEX Alligator®, Water Pump Pliers, self-locking on pipes and nuts; box-joint design; Available with fall protection in the classic 250 mm length and in a 300 mm length for greater leverage
	88 02 300 T black atramentized; head polished	
	95 12 165 T burnished	Cable Shears, precision ground, hardened blades: clean and smooth cut without crushing and deformation
	95 62 190 T head polished	Wire Rope Cutter, forged, Cutter geometry prevents the wire rope fanning out