KNIPEX Tethered Tools, VDE-tested

Flexible drop protection system

- Working at heights and live line working are associated with greater risk
- Using the Tethered Tools versions of the individually tested KNIPEX VDE pliers significantly reduces hazards caused by falling tools
- > 16 different models of insulated KNIPEX pliers available in a Tethered Tools version (others on request)
- > Tool is reliably protected by a tether, adapter strap and
- > Doubly safeguarded work: extremely stable tether attachment welded tightly to the handle, for attaching a tether
- > Tether attachment does not get in the way during unsecured work on the ground
- > Handles with insulating multi-component grips, additionally tested for stress from heat, cold, tension and impact; tested in accordance with DIN EN / IEC 60900, VDE



You can find all models of Tethered Tools from page 8

Article No.	EAN 4003773-	←→ mm	Pliers
03 06 180 T	081395	180	Combination Pliers
08 26 145 T	081401	145	Needle-Nose Combination Pliers
11 06 160 T	081418	160	Insulation Strippers
13 96 200 T	081425	200	Pliers for Electrical Installation
13 66 180 T	081319	180	KNIPEX StriX, Insulation Strippers with Cable Shears
25 06 160 T	081432	160	Snipe Nose Side Cutting Pliers, Radio Pliers
26 16 200 T	081449	200	Snipe Nose Side Cutting Pliers (Stork Beak Pliers), straigt
26 26 200 T	081456	200	Snipe Nose Side Cutting Pliers (Stork Beak Pliers), angled
70 06 160 T	081463	160	Diagonal Cutter
70 06 180 T	081470	180	Diagonal Cutter
73 06 160 T	081487	160	KNIPEX X-Cut® Compact Diagonal Cutter
74 06 200 T	081494	200	High Leverage Diagonal Cutter
74 06 250 T	081500	250	High Leverage Diagonal Cutter
87 26 250 T	081517	250	KNIPEX Cobra® VDE, Hightech Water Pump Pliers
95 16 165 T	081524	165	Cable Shears
97 78 180 T	081531	180	Crimping Pliers for end sleeves (ferrules)