

Features

- Illuminated red rocker switch
- Non latching
- On-Off action
- SPST contact configuration
- Polycarbonate button
- Lamp Tungsten

RS PRO EPDM Rubber Black Lip Gasket

RS Stock No.: 027-3003



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Rocker Switch



Product Description

The RS PRO illuminated rocker switch features a black body with red illumination when in the on position and Silver plated Copper terminals for easy panel mounting in a 20mm panel cut out.

General Specifications

Rating	12VDC 10A
Colour	Black body/Red illuminated
Switch action	SP On-off
Terminal material	Copper alloy SN or AG plated
Housing material	Nylon #66 UL 94V-2
Rocker material	PC UL94HB
Contact material	AgNi (15) Alloy
Lamp	Tungsten
Also available	Double pole versions available

Electrical Specifications

F	
Rating	112VDC 10A
ratifiq	112VDC 10A


Operation Environment Specifications


Maximum contact resistance	30ΜΩ
Minimum insulation resistance	500VDC 100MΩ
Electrical life	10,000 cycles
Lamp life	approx. 2,000 hours
Operation force	300-600gf
Operating temperature	-25°C~125°C





Approvals


Compliance	ROHS compliant
Approval	VDE, UL














20.8 20.8 20.8



Z