

# **Features**

- Illuminated red rocker switch
- Non latching
- Lamp life approx.2,000 hours
- Switch action SP Onoff
- Rating: 24VDC 10A

### **RS PRO Round Rocker Switch**

RS Stock No.: 273-025



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## **Rocker Switches**



#### **Product Description**

The RS PRO illuminated rocker switch features a black body with red illumination when in the on position and Silver plated Copper terminals for easy panel mounting in a 20mm panel cut out.

#### **General Specifications**

Terminal material	Copper alloy SN or AG plated
Colour	Black body/Red illuminated
Switch action	SP On-off
Rocker material	PC UL 94HB
Housing material	Nylon #66 UL 94V-2
Contact material	AgNi (15) Alloy
Lamp	Tungsten
Other Details	Double pole versions available

#### **Electrical Specifications**

Rating	24VDC 10A	


#### **Environmental Operation Specifications**


Maximum contact resistance	30ΜΩ
Minimum insulation resistance	500VDC 100MΩ
Electrical life	10,000 cycles
Lamp life	approx. 2,000 hours
Operation force	300-600gf
Operating temperature	-25°C~125°C





### **Approvals**


Compliance	ROHS compliant
Approval	VDE, UL











Х

20.2

20.4

20.6

