



ENGLISH

Datasheet

Steel Girder Suspension Clip & Hanger, 14 → 20 mm

RS Stock number [277519](#)



Description

- Chain/Wire Hangers
- Either horizontal flange or vertical flange

Specification

- | | |
|----------------------------|------------|
| • Flange Orientation | Horizontal |
| • Flange Thickness | 14 → 20 mm |
| • Flange Thickness Maximum | 20mm |
| • Flange Thickness Minimum | 14mm |
| • Material | Steel |
| • Maximum Load | 90kg |

Measurements

- | | |
|-----------------|---------|
| • T | 14-20mm |
| • \varnothing | 6.5mm |
| • A | 30mm |
| • B | 26.6mm |

