

## FEATURES

- To DIN933
- Grade 8-8 high tensile steel
- Bright zinc plated and clear passivated
- Supplied in a polypropylene case with hinged cover

## 1165 piece Steel Screw/Bolt Kit, M10, M12, M4, M5, M6, M8

RS Stock No.: 278-118



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

From the trusted RS PRO brand, these high-quality hexagon head set screws are ideal for many applications. The grade 8.8 hexagon socket set screws are a fully threaded fastener for reliable fixing with a relevant sized nut. The socket set screws are used to join many kinds of materials together, and are suitable for you to use in a dry, indoor environment.

### General Specifications

<b>Number Of Pieces</b>	1165
<b>Screw/Bolt Type</b>	Set Screw
<b>Drive Type</b>	Hexagon Socket
<b>Kit Contents</b>	1165 Set Screws, Supplied in a Polypropylene Case with Hinged Cover
<b>Grade</b>	8.8
<b>Applications</b>	Machinery, Woodwork, Construction

### Mechanical Specifications

<b>Screw/Bolts Lengths</b>	10mm to 50mm
<b>Thread Size</b>	M10, M12, M4, M5, M6, M8
<b>Material</b>	Steel
<b>Finish</b>	Bright Zinc Plated, Clear Passivated
<b>Screw/Bolt Length Longest</b>	50mm
<b>Screw/Bolt Length Shortest</b>	10mm
<b>Specification</b>	DIN 933

Kit Contents									
Thread Size	L (mm)	Qty	L (mm)	Qty	L (mm)	Qty	L (mm)	Qty	Nuts
M4	10	50	16	50	25	40	-	-	140
M5	12	50	16	50	30	40	-	-	140
M6	16	50	20	40	25	30	-	-	120
M8	12	20	24	25	40	40	40	20	124
M10	20	10	25	16	50	12	-	-	38
M12	20	10	30	10	50	10	-	-	30

