

CA-T2T2-10M-22/3-R-BBG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The right charging cable for every vehicle type
Simple, safe and quick

General ordering data

Version	AC charging cable, Plug type - charging point: Type 2, Plug type - vehicle side: Type 2, Charging power, max.: 22 kW, Number of phases: 3, Rated current: 32 A, Cable length: 10 m, Cable type: regular
Order No.	2791310000
Type	CA-T2T2-10M-22/3-R-BBG
GTIN (EAN)	4064675070788
Qty.	1 pc(s).

Creation date April 21, 2021 3:29:36 PM CEST

CA-T2T2-10M-22/3-R-BBG

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	3,500 g
------------	---------

Temperatures

Storage temperature	-40 °C...70 °C	Humidity at storage temperature	5 - 95% rel. humidity
Operating temperature	-30 °C...55 °C		

Cable

Cable colour	black	Cable length	10 m
Cable type	regular		

Plug type

Plug type - charging point	Type 2	Plug type - vehicle side	Type 2
Plug colour	black, dark grey		

System requirements

Charging power, max.	22 kW	Rated voltage (AC)	480 V
Rated current	32 A	Number of phases	3
Type of communication to vehicle	Control Pilot (CP), Proximity Pilot / Plug Present (PP)	Charging mode	Mode 3
Protection degree	IP54		

Approvals and norms

Approvals	IEC 62196-1, IEC 62196-2, EN 50620
-----------	---------------------------------------

Material data

Max. relative humidity during storage	95 %	Operating temperature, max.	55 °C
Operating temperature, min.	-30 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-40 °C		

Classifications

ETIM 6.0	EC002897	ETIM 7.0	EC002897
ECLASS 9.0	27-14-47-05	ECLASS 9.1	27-14-47-05
ECLASS 10.0	27-14-47-05	ECLASS 11.0	27-14-47-05

Downloads

User Documentation	Safety notes
Brochure/Catalogue	Catalogues in PDF-format

Data sheet

CA-T2T2-10M-22/3-R-BBG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

