

#### **FEATURES**

- Metric threaded rod
- To DIN975 standards
- A2 grade 18/8 stainless steel (Type 304 S15)
- Can be used up to 800°C
- Suitable for use in most food, medical, chemical, construction and electronic applications

# RS PRO Plain Stainless Steel Threaded Rod, M6, 1m

RS Stock No.: 280-408



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### **Product Description**

These 1m stainless steel metric threaded rods are fully threaded and made of A2 grade stainless steel, with a range of thread sizes available: M3 (RS: 280363), M4 (RS: 280379), M5 (RS: 280385), M6 (RS: 280391), M8 (RS: 280408), M10 (RS: 280414), M12 (RS: 280420), M16 (RS: 289089), and M20 (RS: 289095).

#### **General Specifications**

Thread Size	M6	
Material	Stainless Steel	
Stainless Steel Type	A2 304	
Finish	Plain	
Applications	Construction Projects, Woods, Metals,	

#### **Mechanical Specifications**

Thread Length Style	Fully Threaded
Length	1m

#### **Approvals**

Standards Met	DIN 975

## Threaded Rod



RS Stock No.	Size	Length
280363	M3	1m
280379	M4	1m
280385	M5	1m
280391	M6	1m
280408	M8	1m
280414	M10	1m
280420	M12	1m
289089	M16	1m
289095	M20	1m