

SOLID ABS 2819 13 G



Sample photo

Order symbol: ABS 2819 13 G
Product nbr: 5880360
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074039026
EI. number:
 Finland: 3423755
 Electric No. Italy: 7410120
 Electric No. Sweden: 2539709

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions: Length Width Height Accessories:

Dimensions:	Length	Width	Height	Accessories:	
mm:	278	188	130	EKJXT	Mounting plate isolated
inch:	10.9	7.4	5.1	EKV 12	DIN-35 Mounting rail
Materials:				EKV 22	DIN-35 Mounting rail
Material: ABS				EKJZR	Extension frame

Materials:		Rating:	
Material:	ABS	Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262): IK08	
Cover screws material:	Polyamide	Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey	Flammability Rating: UL 94 HB	
Gasket material:	Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 650	
Temperatures:		NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
Temperature °C (short term):	-40 ... 80 °C	Certificates:	
Temperature °C (continuous):	-40 ... 60 °C	SGS Fimko	
Temperature °F (short term):	-40 ... 175 °F	Gost R	
Temperature °F (continuous):	-40 ... 140 °F		

Accessories:

EKJVT Mounting plate

