

FEATURES

- Machine screws to DIN965 & DIN7985 standards
- Nuts to DIN934 standard
- Washers to DIN123 standards
- A2 stainless steel
- Generally nonmagnetic

3168 piece Stainless Steel Screw/Bolt Kit, M2, M2.5, M3, M4, M5, M6

RS Stock No.: 281-984



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From the trusted RS PRO brand, this set of high-quality cross-recess pan and countersunk head machine screws are ideal for many applications. Machine screws are used in threaded holes, which can provide a stronger joint between the screw and the material it is driven into. This, combined with the full screw thread, will therefore translate to a higher quality finish and therefore a higher quality product overall.

General Specifications

Number Of Pieces	3168
Screw/Bolt Type	Machine Screw
Head Shape	Flat, Pan
Drive Type	Pozidriv
Kit Contents	M2- L-6mm Qty 100, L-12mm Qty 100mm, Nuts 200, Washer 200 M2.5- L-6mm Qty 90, L-12mm Qty 90mm, Nuts 140, Washer 140 M3- L-6mm Qty 40, L-10mm Qty 40mm, L-12mm Qty 30mm, L-20mm Qty 30mm, Nuts 385, Washer 385
Applications	Chemical equipment, Food & drug production equipment, Bearing plates, Heat Exchanger tubes, Pumps & valves



Mechanical Specifications

Screw/Bolts Lengths	6mm to 25mm
Thread Size	M2, M2.5, M3, M4, M5, M6
Material	Stainless Steel
Stainless Steel Type	304, A2
Finish	Plain
Screw/Bolt Length Longest	25mm
Screw/Bolt Length Shortest	6mm
Specification	DIN 965, DIN 7985, DIN 934, DIN 125A, DIN 125B

Kit Conte	Kit Contents										
Head Type	Thread Size	L (mm)	Qty	L (mm)	Qty	L (mm)	Qty	L (mm)	Qty	Nuts	Washers
Slotted Pan	M2	6	100	12	100	-	-	_	-	200	200
Slotted Pan	M2·5	6	90	12	90	-	-	_	-	140	140
Slotted Pan	М3	6	40	10	40	12	30	20	30	385	385



- GB Machine Screw Kit ISO Metric (Pozidriv) Stainless Steel
- D ISO metrisches Maschinenschrauben-Sortiment (Pozidriv) Rostfreier Stahl
- F Kit de vis au pas metrique a empreinte cruciforme en acier inoxydable A2
- Corredo di vita a macchina metriche ISO (pozidriv) in acciaio inossidabile
- Juego de tornillos para metales, ISO, de rosca métrica (pozidriv), acero inoxidable



				(\$)	T			
	Ĩ							
M5 x 12 20 M5 x 16 12 M5 x 25 12	M4 x 10 50 M4 x 16 20 M4 x 25 15	M3 x 10 40 M3 x 12 30	M3 x 6 40 M3 x 20 30	M2.5 x 6 90 M2.5 x 12 90	M2 x 6 100 M2 x 12 100			
				Ī				
M6 x 12 10 M6 x 20 10 M6 x 25 10	M5 x 12 20 M5 x 20 10 M5 x 25 15	M4 x 12 40 M4 x 16 30 M4 x 20 20	M3 x 6 60 M3 x 12 80 M3 x 20 40	M6 x 25 10	M6 x 12 15 M6 x 16 10			
M6 65 65 65	M5	M4 💮 175 M4 🌀 175	M3	M2.5 140 M2.5 140	M2			





