

FEATURES

- Screw affixing method
- Clamp width of 10 mm
- Bright Zinc Plated (BZP)

RS PRO Cable Clip Black Screw Plated Steel P Clamp, 40mm Max. Bundle

RS Stock No.: 287-5581



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Cable Clips & Clamps



Product Description

From RS PRO, this robust P Clip is ideal for securely holding pipes, cables and hoses in permanent or semi-permanent installations. The plated steel clip has a rubber insert which offers a secure grip which minimizes shifting. The clamp simply wraps around the cable or conduit, and screws together into a fixed surface. This simple affixing method ensures versatility as to where the clamp can be placed.

General Specifications

| Material | Plated Steel |
|------------------------|--|
| Colour | Black |
| Affixing Method | Screw |
| Cable Clip/Clamp Style | P-clamp |
| Finish | Bright Zinc Plated |
| UV-Resistant | No |
| Applications | P clips, or pipe clips, are used whenever fasteners are need to secure lengths of flexible conduit or cable to a fixed position. They can be used in the automobile industry or wherever rubber or plastic hosing needs to be held in place. |

Mechanical Specifications

| Dimensions | 19.1mm x 2.4mm | | | |
|-------------------------|----------------|--|--|--|
| Width | 19.1mm | | | |
| Depth | 2.4mm | | | |
| Maximum Bundle Diameter | 40mm | | | |



Operation Environment Specifications

| Maximum Temperature | -25°C |
|---------------------|-------|
| Minimum Temperature | 105°C |


Approvals

| Compliance/Certifications | RoHS certificate of compliance |
|---------------------------|--------------------------------|









| PART No | А | В | С | D | ØΕ | F |
|----------|------|------|-----|------|------|-----|
| 186-5353 | 13.5 | 12.7 | 3.5 | 9.5 | 5.2 | 1.4 |
| 186-5375 | 15.3 | 12.7 | 3.5 | 14.0 | 5.2 | 1.4 |
| 186-5381 | 17.3 | 12.7 | 3.5 | 17.0 | 5.2 | 1.4 |
| 186-5397 | 19.3 | 12.7 | 3.5 | 21.0 | 5.2 | 1.4 |
| 186-5404 | 21.5 | 12.7 | 3.5 | 25.5 | 5.2 | 1.4 |
| 186-5410 | 25.8 | 12.7 | 3.5 | 34.0 | 5.2 | 1.4 |
| 287-5581 | 37.3 | 19.1 | 4.5 | 44.5 | 10.2 | 2.4 |
| 287-5597 | 43.5 | 25.4 | 4.5 | 57.2 | 14.2 | 2.4 |