

PRODUCT-DETAILS

# E 91/32

## E 91/32 Fuse switch disconnecter



### General Information

Extended Product Type	E 91/32
Product ID	2CSM200923R1801
EAN	8012542009238
Catalog Description	E 91/32 Fuse switch disconnecter
Long Description	E 91/32 is a fuseholder for overcurrent and short circuit protection. No blown fuse indicator.

### Technical

Standards	IEC 60947-3
Rated Voltage ( $U_r$ )	acc. To IEC 400 V acc. To UL 690 V
Rated Operational Voltage	AC-20B 690 V IAC-22B 400 V
Rated Insulation Voltage ( $U_i$ )	1 kV
Rated Frequency (f)	50/60 Hz
Power Loss	at Rated Operating Conditions per Pole 3 W
Number of Poles	1
Number of Protected Poles	1
Tightening Torque	2...2.5 N·m
Utilization Category	Connecting and disconnecting under no-load conditions - occasional actuation (AC-20B) Switching of mixed resistive and inductive loads, including moderate overloads - occasional actuation (AC-22B)

Lock Type	Padlockable when open
Mounting Type	DIN rail
Sealing Type	Sealing Wire
Material of Conductor	Copper
Options Provided	No
Recommended Screw Driver	Pozidriv 2
Shock and Vibration Withstand acc. to IEC 61373	Category 1, Class B
Connecting Capacity	Rigid 2x5 mm <sup>2</sup> Stranded 2x2-5 mm <sup>2</sup>
Fuse Size	10x38 mm max. 90% with temp. +20 °C 50% with max. temp. +40 °C
Rated Operational Current AC (I <sub>e</sub> )	32 A

## Environmental

Ambient Air Temperature	Operation -5...+40 °C Storage -25...+70 °C
Degree of Protection	IP20
Maximum Operating Altitude Permissible	2000 m
Resistance to Vibrations acc. to IEC 60068-2-6	2 to 13 Hz x= 1 mm peak 13 to 100 Hz y= 0.7 g peak
Resistance to Shock acc. to IEC 60068-2-27	15g / 18 shocks / 13 ms
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	See RoHS Information

## Technical UL/CSA

Connecting Capacity UL/CSA	Rigid 2x10 AWG Stranded 2x14-10 AWG
----------------------------	--

## Dimensions

Width in Number of Modular Spacings	1
Product Net Width	0.018 m
Product Net Height	0.085 m
Product Net Depth / Length	0.064 m
Product Net Weight	0.061 kg
Dimensions	1 module
Built-In Depth (t <sub>2</sub> )	64 mm

## Container Information

Package Level 1 Units	box 6 piece
Package Level 1 Width	0.105 m
Package Level 1 Height	0.085 m
Package Level 1 Depth / Length	0.064 m
Package Level 1 Gross Weight	0.369 kg

Package Level 1 EAN	8012542009245
Package Level 2 Units	box 6 piece
Package Level 2 Width	105 mm
Package Level 2 Height	85 mm
Package Level 2 Depth / Length	64 mm
Package Level 2 Gross Weight	369 g
Package Level 2 EAN	8012542009245

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85361010
E-Number (Finland)	3017004
E-Number (Sweden)	2318050
Country of Origin	Romania (RO)

## Certificates and Declarations (Document Number)

BV Certificate	9AKK108467A0330
CCC Certificate	9AKK108467A0340
Certification Agency	IMQ, BV, Korean register, CCC, EAC, UL
Declaration of Conformity - CE	9AKK106713A5623
EAC Certificate	9AKK107992A1034
Environmental Information	See RoHS Information
IMQ Certificate	9AKK108467A0324
Instructions and Manuals	No document needed
KRS Certificate	9AKK108467A0337
LR Certificate	9AKK107991A7313
RoHS Information	2CSC444011K2701
UL Certificate	9AKK107992A1039

## Popular Downloads

Data Sheet, Technical Information	2CSC444002B0204
Instructions and Manuals	No document needed

## Classifications

ETIM 7	EC002705 - Holder for cylindrical fuse
ETIM 8	EC002705 - Holder for cylindrical fuse
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	85361010
Object Classification Code	F

## Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CSM277333R1801	E 9F10 GG05 Fuse link	E 9F10 GG05	1	piece
2CSM277113R1801	E 9F10 GG1 Fuse link	E 9F10 GG1	1	piece
2CSM258723R1801	E 9F10 GG2 Fuse link	E 9F10 GG2	1	piece
2CSM257543R1801	E 9F10 GG4 Fuse link	E 9F10 GG4	1	piece
2CSM256363R1801	E 9F10 GG6 Fuse link	E 9F10 GG6	1	piece
2CSM258633R1801	E 9F10 GG8 Fuse link	E 9F10 GG8	1	piece
2CSM257453R1801	E 9F10 GG10 Fuse link	E 9F10 GG10	1	piece
2CSM256273R1801	E 9F10 GG12 Fuse link	E 9F10 GG12	1	piece
2CSM277543R1801	E 9F10 GG16 Fuse link	E 9F10 GG16	1	piece
2CSM277323R1801	E 9F10 GG20 Fuse link	E 9F10 GG20	1	piece
2CSM277103R1801	E 9F10 GG25 Fuse link	E 9F10 GG25	1	piece
2CSM258713R1801	E 9F10 GG32 Fuse link	E 9F10 GG32	1	piece
2CSM257473R1801	E 9F10 AM05 Fuse link	E 9F10 AM05	1	piece
2CSM256293R1801	E 9F10 AM1 Fuse link	E 9F10 AM1	1	piece
2CSM277563R1801	E 9F10 AM2 Fuse link	E 9F10 AM2	1	piece
2CSM277343R1801	E 9F10 AM4 Fuse link	E 9F10 AM4	1	piece
2CSM277123R1801	E 9F10 AM6 Fuse link	E 9F10 AM6	1	piece
2CSM258733R1801	E 9F10 AM8 Fuse link	E 9F10 AM8	1	piece
2CSM257553R1801	E 9F10 AM10 Fuse link	E 9F10 AM10	1	piece
2CSM256373R1801	E 9F10 AM12 Fuse link	E 9F10 AM12	1	piece
2CSM258643R1801	E 9F10 AM16 Fuse link	E 9F10 AM16	1	piece
2CSM257463R1801	E 9F10 AM20 Fuse link	E 9F10 AM20	1	piece
2CSM256283R1801	E 9F10 AM25 Fuse link	E 9F10 AM25	1	piece
2CSM277553R1801	E 9F10 AM32 Fuse link	E 9F10 AM32	1	piece
2CCS500900R0181	ZLS725 Spare parts	ZLS725	1	pack
2CCS400900R0091	ZLS726 Spare parts	ZLS726	1	pack

## Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Protection and Safety Devices → Cylindrical Fuse Holders and Fuse Switch Disconnectors

