268 HANDHELD CASES

- 318
- 342




370

2U Raspberry Pi 4B enclosure with fan vent

Product overview

Clip together 2-U-Shell enclosure for the Raspberry Pi 4B. Manufactured using robust 3mm textured UL94-HB HIPS.

- Pi 4B PCB fits into grooves (no screws)
- Venting on top of case
- GPIO ribbon cable slot on the underside
- CSI slot for camera cable
- · Rear slots for SD card and LEDs
- · Supplied with push fit rubber feet
- · Fan fixing holes can be easily knocked out using screws
- · Recommended for use with a 30mm fan
- · In house testing of the PCU to operating temperature of 44°C, when used in conjunction with a fan
- Compatible with Pi HAT POE
- Also available in high temperature ABS (subject
- Transform your Raspberry Pi enclosure into a DIN Rail mountable solution with our CDR-Bracket (not included).









Raspberry Pi 4 PCB not included

PART NO.	COLOUR	MATERIAL TYPE	MATERIAL TEMPERATURE	UL RATING	MATERIAL THICKNESS	DIMENSIONS
CBRPI4B-2U-BK	Black	High impact polystyrene	Rated for use up to 70°C	НВ	3mm	L 89.3mm x W 62.4mm x H 34mm
CBRPI4B-2U-WH	White	High impact polystyrene	Rated for use up to 70°C	НВ	3mm	L 89.3mm x W 62.4mm x H 34mm
CBRPI4B-2U-DG	Dark grey	High impact polystyrene	Rated for use up to 70°C	НВ	3mm	L 89.3mm x W 62.4mm x H 34mm

KEY FEATURES

Clip-together design | Raspberry Pi 4B clips in without screws Vents in the top for heat dissipation



ACCESSORIES

DIN Rail mount bracket

· Screws included



PART NO.	DESCRIPTION
CDR-Bracket	DIN Rail mount bracket