



3-0641-ESD

ESD MINI SIDE CUTTERS FULL FLUSH FOR CU-WIRE UP TO Ø 1.0 MM

Full Flush (without side face, cut completely flush)

cutting capacity soft/medium/hard/piano Ø in mm: 1.0/0/0/0

head width 10 mm

blade length 10 mm

material tool steel (HRC 56-58)

surface burnished

ESD handle black $10^6 - 10^9$ ohm

length 135 mm

weight 70 g

AREA OF APPLICATION

Electronic side cutters with spring, without cutting edge, for CU wires up to \varnothing 1.0 mm / up to 18 AWG.