



ENGLISH

RS Pro Fahrenheit/Centigrade Dial Clip On Dry Thermometer Suitable For Various Applications

RS Stock No. 324-8558

Brand RS Pro



Product Details

63mm Clip on Pipe Thermometer

Designed to indicate surface temperature of pipework. Applications include boiler pipework, radiators, process pipelines

Held in place by wrap around spring

No need to drill pipe work

Glass Window

Thermometers - Surface Contact Type

66mm diameter thermometers with Bi-metal movement.

Specifications

Not what you're looking for? Select the attributes you require, then click the button below

<input type="checkbox"/>	Thermometer Type	Dial
<input type="checkbox"/>	Fixing Method	Clip On
<input type="checkbox"/>	Suitable Applications	Boiler Pipe Work, Process Pipeline, Radiator
<input type="checkbox"/>	Temperature Scale	Both
<input type="checkbox"/>	Filling Type	Dry
<input type="checkbox"/>	Case Material	Steel
<input type="checkbox"/>	Case Diameter	63mm
<input type="checkbox"/>	Maximum Temperature Sensed	+120°C
<input type="checkbox"/>	Minimum Temperature Sensed	0°C
<input type="checkbox"/>	Temperature Sensitive Range	0 → +120°C