

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0334824801](#)
Status: **Active**
Overview: [MX150 Sealed and Unsealed Connector System](#)
Description: MX150 Sealed Male Connector, Dual Row, 8 Circuits, Polarization A, without Connector Position Assurance, Black

Documents:

3D Model	Application Specification AS-33472-100-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31300-635-001 (PDF)
Product Specification PS-33472-000-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	33482
Application	Power, Wire-to-Wire
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	889056543590


Physical

Circuits (maximum)	8
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	11.410/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-33472-100-001
Packaging Specification	PK-31300-635-001
Product Specification	PS-33472-000-001
Sales Drawing	SD-33482-0001-001, SD-33482-0002-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[33482](#) Series

Mates With

[33472](#) Female Dual Row Sealed Connector

Use With

[33000](#) MX150 Tin (Sn) Male Terminal, [33011](#) Gold (Au) Male Terminal, [343450001](#) MX150 Sealed Blade Cavity Plug