



# TRIAx

connecting the future



## IFP 522 Power Supply/Inserter +12Vdc - for UFO150

Article number: 339522

### Product description:

#### IFP 522 Power Supply / Inserter

- 12 VDC / 85mA output on RF input for UFO 150
- Automatic switch from 12 VDC to 220 VAC input upon availability
- 1 x RF F-connector input from UFO 150 (12 VDC / 85 mA)
- 2 x RF F-connector outputs for 2 x TV sets.
- Signal insertion loss: 4dB.
- Quick and easy installation
- Install instruction already available on UFO 150 box and manual
- Single packed in compact color retail cardboard box.

### Specifications

ORDER INFORMATION	
EAN Number	5702663395220
CHARACTERISTICS	
Type	Power supply
FREQUENCY	
Frequency range	47-862 MHz

LOSS	
Through loss	4 dB
ELECTRICAL	
Impedance	75 $\Omega$
OPERATIONAL	
AC Supply voltage	230 VAC
Power Consumption (typ.)	3 W
PSU output DC voltage	12 VDC
PSU output max. DC current	85 mA
CONNECTORS	
Connector Type	F-female
Number of inputs	2
Number of outputs	2
MECHANICAL	
Colour	White
Packing QTY	1
Packaging Height	0,070 m
Packaging Width	0,110 m
Packaging Depth	0,150 m
Packaging Volume	0,001 m <sup>3</sup>
Net Weight	0,315 kg
Tara Weight	0,030 kg
Total Weight	0,345 kg
Remarks	f-connector/DC jack and red/black cable for battery