

## Between Series Adaptor 33\_BNC-A-0-1/0--\_ -

### Description

Adaptor plug/jack  
BNC plug (male) / A jack (female)

Interface standards  
Series BNC - IEC 61169-8\_MIL-STD-348A/301\_CECC 22120  
Series A - SUHNER-A



### Technical Data

#### Electrical Data

Impedance other  $\Omega$   
Interface frequency max. 4 GHz

#### Mechanical Data

Number of matings 500  
Weight 0.0192 kg

#### Environmental Data

Operating temperature -20 °C to 85 °C  
2011/65/EC (RoHS) compliant

#### Material Data

Interface - BNC plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - A jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	Silver Plating
Body	Bronze	
Insulator	PFA / PTFE	

### Related Documents

Outline drawing DOU-00014399

### Ordering Information

Single package 33\_BNC-A-0-1/0--\_ -E