

## **FEATURES**

- Cat5e RJ45 coupler
- 8P8C socket to 8P8C socket
- 50µ gold plated contacts
- Wired straight contact 1 to contact
  1, etc
- For shielded twisted pair (STP) cables and patch leads
- Meets C5e EIA/TIA 568B Standard
- Dimensions: 25 x 25 x 45 mm

# RS PRO Cat5 RJ45 Female Coupler, STP

RS Stock No.: 340-9630



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### **Product Description**

From RS PRO, this Cat5e RJ45 coupler allows for versatile cable management in a home or workplace network. The in-line female coupler is able to connect two ethernet patch leads, allowing more distance and freedom from wall sockets or connecting devices. Compact and robust, the socket to socket RJ45 adapter also features gold plated contacts for assured connectivity. It is compatible with shielded twisted pair cables (STP) to maintain a level of protection against signal interference

#### **General Specifications**

Туре	Coupler
Interface Type	RJ45 Female
LAN Category	Cat5e
Shield Type	STP
Wiring Configuration	Straight Through
Colour	Black
Contact plating	Gold
Application	Domestic Office setups, Call Centres, Servers


#### **Mechanical Specifications**

Length	25mm
Width	25mm
Depth	45mm

#### **Approvals**

Compliance/Certifications	C5e EIA/TIA 568B





0