

Datasheet

**RS Pro Temperature Probe, K, -200 to +1100 °C**

RS Stock No: **342-9151**



## Product Details

RS Pro temperature probe uses type K sensor for the measurement of temperatures up to +1100°C. This probe application kit is designed to provide a family of sensor well suited for particular applications. The plug-mounted probes may be used by themselves or in conjunction with the sockets in the handle to provide greater flexibility of use. The kit contains type K probes, socket in the handle, plug mounted ribbon surface probe, plug mounted mineral insulated probe, plug mounted air probe and hook and loop probe.

## Features and Benefits

- Fine wire
- 2 m long cable
- Miniature plug
- Accuracy of  $\pm 0.25\%$



**Specifications:**

Best Accuracy	±0.25%
Cable Length	2 m
Connector Type	Miniature Plug
Maximum Temperature Measurement	+1100°C
Probe Type	Air, Surface
Sensor Type	K