LG 34WN80C-B 86.4 cm (34") 3440 x 1440 pixels UltraWide Quad HD Black



Brand : LG

Product code: 34WN80C

Product name : 34WN80C-B

- 34” 21:9 Curved WQHD (3440 x 1440) IPS Display
- sRGB 99% Color Gamut
- USB-C with 60W PD
- HDR 10
- 3-Side Virtually Borderless Design
- Tilt / Height Adjustable Stand

34”, 21:9, 3440 x 1440, IPS Display, sRGB 99%, USB-C, HDR 10
LG 34WN80C-B. Display diagonal: 86.4 cm (34"), Display resolution: 3440 x 1440 pixels, HD type: UltraWide Quad HD, Response time: 5 ms, Native aspect ratio: 21:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in USB hub. VESA mounting, Height adjustment. Product colour: Black





Display	
Display diagonal *	86.4 cm (34")
Display brightness (typical)	300 cd/m²
Display resolution *	3440 x 1440 pixels
Native aspect ratio *	21:9
Response time	5 ms
HD type *	UltraWide Quad HD
Screen shape *	Flat
Supported graphics resolutions	3440 x 1440
Aspect ratio	21:9
Contrast ratio (typical) *	1000:1
Maximum refresh rate *	60 Hz
Viewing angle, horizontal	178°
Viewing angle, vertical	178°
Panel type *	IPS
Response time (fast)	5 ms
Pixel pitch	0.2325 x 0.2325 mm
RGB colour space	sRGB
sRGB coverage (typical)	99%

Design	
Product colour *	Black

Ports & interfaces	
Built-in USB hub *	✓
USB upstream port type	USB Type-C
USB Type-C downstream ports quantity	1
HDMI *	✓
HDMI ports quantity	2
DisplayPorts quantity	1
Headphone out *	✓
Headphone outputs	1

Ergonomics	
Panel mounting interface	100 x 100 mm
VESA mounting *	✓
Height adjustment *	✓
Tiltable	✓

Power	
Energy efficiency class (SDR) *	G
Energy efficiency class (HDR) *	G
Energy consumption (SDR) per 1000 hours *	40 kWh
Energy consumption (HDR) per 1000 hours *	57 kWh
AC input voltage	100 - 240 V
AC input frequency	50/60 Hz
Energy efficiency scale	A to G

Weight & dimensions	
Width (with stand)	812.8 mm
Depth (with stand)	228.6 mm
Height (with stand)	558.8 mm
Weight (with stand)	7.71 kg
Width (without stand)	81.3 cm
Depth (without stand)	35.6 cm
Height (without stand)	7.62 cm
Weight (without stand)	5.9 kg

Packaging data	
Stand included	✓
Package width	965.2 mm
Package depth	203.2 mm
Package height	508 mm
Package weight	11.8 kg
Package type	Box

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 30-NOV-2021. Prints or copies of Information are only valid on the printed Publication date